

Garant

Steel boring bar A.. SVVCR 72,5°, for indexable inserts VC.., right-hand, Shank Ø / insert size: 20/11mm


Order data

Order number	261352 20/11
GTIN	4045197713629
Item class	21T

Technical description

suitable indexable insert	VC.. 1103..
Head length L_1	50 mm
ISO code toolholder	A20Q SVVCR/L11
Pack of insert screws	269028 22
Neck width L_4	13.9 mm
Minimum pre-drill $\varnothing D_{min}$	25 mm
Insert size	11 mm
Centre offset L_3	14 mm
Overall length L	180 mm
Clamping height L_2	19 mm
Setting angle κ	72.5 degrees
Usable depth T	9,5 mm
Shank $\varnothing D_s$	20 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15