

Garant

Steel boring bar A.. SVVCL 72,5°, for indexable inserts VC., left-hand, Shank Ø / insert size: 16/11mm


Order data

Order number	261353 16/11
GTIN	4045197713643
Item class	21T

Technical description

suitable indexable insert	VC.. 1103..
Pack of insert screws	269028 22
Head length L ₁	40 mm
Neck width L ₄	11.9 mm
Centre offset L ₃	14 mm
Insert size	11 mm
ISO code toolholder	A16M SVVCR/L11
Minimum pre-drill Ø D _{min}	23 mm
Overall length L	150 mm
Clamping height L ₂	15.5 mm
Setting angle κ	72.5 degrees
Usable depth T	9,5 mm
Shank Ø D _s	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15