

Garant

Steel boring bar A.. SVVCR 72,5°, for indexable inserts VC.., right-hand, Shank Ø / insert size: 16/11mm


Order data

Order number	261352 16/11
GTIN	4045197713612
Item class	21T

Technical description

Insert size	11 mm
Minimum pre-drill $\varnothing D_{\min}$	23 mm
Head length L_1	40 mm
Pack of insert screws	269028 22
suitable indexable insert	VC.. 1103..
ISO code toolholder	A16M SVVCR/L11
Centre offset L_3	14 mm
Neck width L_4	11.9 mm
Overall length L	150 mm
Clamping height L_2	15.5 mm
Setting angle κ	72.5 degrees
Usable depth T	9,5 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15