

Garant
**Clamping toolholder STGCR 90°, for indexable inserts TC., right-hand,
Shank / insert size: 16/16mm**

Order data

Order number	260906 16/16
GTIN	4045197713254
Item class	21T

Technical description

Functional width L_4	20 mm
ISO code toolholder	STGCR/L 1616H16
Head length L_1	22 mm
suitable indexable insert	TC.. 16T3..
Pack of insert screws	269028 2
Insert size	16 mm
Shank size	16 mm
Shim screw	269013 2
Shim	269005 7
Overall length L	100 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle κ	90 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 7	269005 7
Set of insert screws Type 18	269028 18
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15