



## Fleece finishing belt (A), 20×520 mm, Grit equivalent: 280



### Order data

Order number	558481 280
GTIN	4045197719294
Item class	52E

### Description

#### Version:

Synthetic nylon non-woven fabric with synthetic resin bonded abrasive grit, long service life, **consistent surface finish, low heat generation.**

#### Application:

For rubbing down rough ground or brushed surfaces, for consistent and reproducible results. Also suitable for removing rust film, light soiling, and discolouration.

Iron, sulphur and chlorine constituents: < 0.1 %

Grit designation: very fine

Version: A very fine

Colour: blue

### Technical description

Grit equivalent	280
Colour	blue
Grit designation	very fine
Version	A very fine

Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %
Linishing belt width	20 mm
Linishing belt length	520 mm
Product name attribute	20×520 mm
Type of product	Fleece linishing belt

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable only under restricted conditions	15-20 m/s	
Steel < 900 N/mm <sup>2</sup>	suitable	10 m/s	P
Steel < 1400 N/mm <sup>2</sup>	suitable	10 m/s	P
Steel < 55 HRC	suitable	10 m/s	H
Steel < 60 HRC	suitable	10 m/s	H
Steel < 67 HRC	suitable	10 m/s	H
INOX	suitable	10 m/s	
Ti	suitable	10 m/s	
GG(G)	suitable	10 m/s	K
CuZn	suitable	10 m/s	N
Plastic, GRP	suitable	10 m/s	
Wood	suitable	10 m/s	
Paint	suitable	10 m/s	
Uni	suitable	10 m/s	
dry	suitable		