

Garant**ER clamping nut Internal, for ER: 25****Order data**

Order number	309621 25
GTIN	4062406093457
Item class	31Z

Description**Version:**

Thread and taper ground in a single setup for highest concentricity.
Internal clamping nut with an external thread. **With slots.**

Suitable for:

ER collet chucks with internal thread.

Optional extras:

Single open ended spanner (for size 16), No. 613300 size 25.

Sealing rings No. 309625; 309630; 309635; 309645.

Note:

Collet chuck and clamping nut are balanced separately!

Technical description

maximum tightening torque	55 Nm
External Ø D	32 mm
Thread	M32×1.5
Width across flats AF	24 mm

Overall length L	14.5 mm
for ER	25 mm
Standard	DIN 6499 D
Type of product	Clamping nut