

**Garant****Tape measure, Band length: 2m****Order data**

Order number	462070 2
GTIN	4062406095505
Item class	41H

**Description****Version:**

A particularly high-quality tape measure with a body made from glass-fibre-reinforced polyamide and automatic tape return. For the perfect grip, the contact areas and stop button are coated with **2-component Haptoprene**. Plain bearings with Teflon ensure smooth action and exceptionally easy running. **Innovative dampers** of special rubber absorb the reaction energy and protect the wrist. **Aluminium profile** inserted on the underside for precise standing. A special clear lacquer protects the tape against wear. The additional anti-glare correction ensures clear visibility under all light conditions.

**Technical description**

Band length	2 m
Tape width	13 mm
Body height	59 mm
Body width	26 mm
Body length	62 mm
Standard	EG I
Calibration	G1

Type of product

Measuring tape

---

**Services**

CalibrationTape measure maximum length 2 m

026240 2