

**Velour-backed abrasive disc (A) 15 holes, Ø 150 mm, Grit: 60****Order data**

Order number	567790 60
GTIN	4045197718426
Item class	52M

Description**Version:**

Velour-backed abrasive disc with **paper backing**. Dust-repellent coating prevents premature clogging. The back is covered with velour loops.

Velour-backed abrasive disc with semi-open distribution, aluminium oxide (A).

Application:

On **orbital sanders** with hook and loop pads e.g.No. 567990 (dust extraction available).

Universal **all-round product** for coarse, intermediate and fine abrasion on all metal and plastic surfaces, paint systems and woods.

maximum circumferential speed: 40 m/s

Technical description

Grit	60
Disc Ø	150 mm
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %

Product name attribute	Ø 150 mm
Number of dust extraction holes	15
Propulsive equipment	Orbital sander
maximum circumferential speed	40 m/s
Type of product	Velour-backed abrasive disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable only under restricted conditions		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Paint	suitable		
Uni	suitable		
dry	suitable		

Accessories

PU hook and loop backing pad Multiple holes Outer Ø 150 mm	567887 150
Multi-hole PU backing pad External Ø 147 mm	567990 147

PU hook and loop backing pad External Ø 150 mm

567885 150