

Garant

**Steel boring bar A.. SDQCR 107,5°, for indexable inserts DC., right-hand,
Shank Ø / insert size: 1012/07mm**


Order data

Order number	260340 1012/07
GTIN	4062406099114
Item class	21T

Technical description

ISO code toolholder	A1012K SDQCR/L07
Minimum pre-drill $\varnothing D_{\min}$	15.5 mm
Head length L_1	27.5 mm
Neck width L_4	10.7 mm
Centre offset L_3	9 mm
Clamping height L_2	11 mm
Pack of insert screws	269028 7
suitable indexable insert	DC.. 0702..
Setting angle κ	107.5 degrees
Insert size	7 mm
Overall length L	125 mm
Usable depth T	4 mm
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8