

Garant

**Steel boring bar A.. SDQCR 107,5°, for indexable inserts DC., right-hand,
Shank Ø / insert size: 1216/07mm**


Order data

Order number	260340 1216/07
GTIN	4062406099121
Item class	21T

Technical description

Head length L_1	39.5 mm
ISO code toolholder	A1216M SDQCR/L07
Setting angle κ	107.5 degrees
Minimum pre-drill $\varnothing D_{\min}$	19.5 mm
Centre offset L_3	11 mm
Neck width L_4	12 mm
Pack of insert screws	269028 7
Overall length L	150 mm
Insert size	7 mm
suitable indexable insert	DC.. 0702..
Clamping height L_2	15 mm
Usable depth T	5 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3xD

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8