

**Garant**

**Steel boring bar A.. SDQCL 107,5°, for indexable inserts DC., left-hand, Shank Ø / insert size: 0810/07mm**


**Order data**

Order number	260341 0810/07
GTIN	4062406099138
Item class	21T

**Technical description**

Clamping height $L_2$	9 mm
Overall length L	100 mm
Head length $L_1$	22.4 mm
Pack of insert screws	269028 7
Neck width $L_4$	8.4 mm
suitable indexable insert	DC.. 0702..
ISO code toolholder	A0810H SDQCR/L07
Setting angle $\kappa$	107.5 degrees
Centre offset $L_3$	6.4 mm
Minimum pre-drill $\varnothing D_{\min}$	12.5 mm
Insert size	7 mm
Usable depth T	3 mm
Shank $\varnothing D_s$	10 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD

Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8