

**ER collet, ER 16, Nominal clamping Ø d: 7/64mm****Order data**

Order number	308920 7/64
GTIN	4062406103774
Item class	32Z

Description**Version:**

Through hardened and ground. Polished.

Note:

The collet clamping Ø range is always up to 1 mm less than nominal, e.g. Ø 10 – 9 mm, except for Ø 1, 1.5 and 2 (where it is only 0.5 mm).

Collets ER16, ER25 and ER32 without a seal also available in inch sizes via the eShop.

Concentricity: ≤ 10 µm

Overall length L: 27.5 mm

Technical description

Adapter	ER 16
Standard	ISO 15488-B
Concentricity	≤ 10 µm
Type	426 E
External Ø D	17 mm
Overall length L	27.5 mm
Type of product	Clamping head

