


**ER collet, ER 16, Nominal clamping  $\varnothing$  d: 5/32mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 308920 5/32   |
| GTIN         | 4062406103798 |
| Item class   | 32Z           |

**Description**
**Version:**

Through hardened and ground. Polished.

**Note:**

The collet clamping  $\varnothing$  range is always up to 1 mm less than nominal, e.g.  $\varnothing$  10 – 9 mm, except for  $\varnothing$  1, 1.5 and 2 (where it is only 0.5 mm).

Collets ER16, ER25 and ER32 without a seal also available in inch sizes via the eShop.

Concentricity:  $\leq 10 \mu\text{m}$

Overall length L: 27.5 mm

**Technical description**

|                          |                       |
|--------------------------|-----------------------|
| Adapter                  | ER 16                 |
| Standard                 | ISO 15488-B           |
| Concentricity            | $\leq 10 \mu\text{m}$ |
| Type                     | 426 E                 |
| External $\varnothing$ D | 17 mm                 |
| Overall length L         | 27.5 mm               |
| Type of product          | Clamping head         |

