

**Boring bar blank Form A, BT 40, Dimension A: 250mm****Order data**

Order number	302889 250
GTIN	4062406105044
Item class	32A

**Description****Version:**

Taper with collar, hardened and ground. Soft shank for further machining.

**Optional extras:**

Pull studs (PS) No. 308760 – 308802.

**Technical description**

Overhang dimension A	250 mm
External $\varnothing$ D	63 mm
Clamping $\varnothing$ D <sub>1</sub>	63 mm
Adapter	BT 40
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Shape	A
Type of product	Boring bar blank

**Accessories**

Pull stud 60°sealed suitable for steep tapers 40	308785 40
--	-----------

Pull stud 45°sealed suitable for steep tapers 40	308765 40
Wrench for pull studsDIN ISO 7388-1 (formerly DIN 69872) suitable for ISO taper size 40	308820 40
Pull stud 45°sealed suitable for steep tapers 40	308760 40
Wrench for pull studsISO 7388 suitable for ISO taper size 40	308830 40
Hurco 45° pull stud with 4-mm bore and fitsealed suitable for steep tapers 40	308801 40
Pull stud Hurco 90° with fitsealed suitable for steep tapers 40	308806 40
Pull stud 90°sealed suitable for steep tapers 40	308795 40
Pull stud Hurco 45° with fitsealed suitable for steep tapers 40	308802 40
Pull stud 90°sealed suitable for steep tapers 40	308790 40