

HOLEX**Plain arbor for screw-in milling cutters, $\varnothing d = 25$ mm, Thread M \times Length L2:
M12X77****Order data**

Order number	301354 M12X77
GTIN	4062406107475
Item class	32A

Description**Version:****Shank tolerance h6.****Application:**

For mounting shrink-fit chucks.

Technical description

L ₂	77 mm
Bore $\varnothing D_1$	12.5 mm
Reach L ₁	87.5 mm
$\varnothing D_2$	21 mm
Overall length L	240 mm
Adapter	$\varnothing d = 25$ mm
Through-coolant	yes
Type of product	Threaded copy mill arbor