



Small pipe cutter with 4 guide rollers



Order data

Order number	818305
GTIN	4045197721464
Item class	82A

Description

Version:

Die-cast magnesium body, enclosed spindle and precision telescopic guide. **4 guide rollers** (secure support even for large \varnothing) with recess. Ergonomic **handle with spare cutter wheel** No. 819100. Manual deburrer **retractable into the body**.

Application:

General purpose for cutting **copper, aluminium, and thin-walled stainless steel pipes**.

Spare part:

Spare pin No. 818020 for cutter wheel No. 819100.

See No. 838510 size S10 for blades for the manual deburrer.

Technical description

Cutter wheel \varnothing	20 mm
Cutter wheel bore	5 mm
Cutter wheel width	5 mm
for pipe outer \varnothing	3 - 35 mm
Type of product	Pipe cutters

Accessories

Wheel pin	818020
Stainless steel inner / outer deburrer for pipe Ø up to 35 mm	814920 35
Spare cutter wheel	819100