

Garant
**Clamping toolholder PCBNR 75°, for indexable inserts CN., right-hand,
Shank / insert size: 40/19mm**

Order data

Order number	250020 40/19
GTIN	4062406119232
Item class	21T

Technical description

suitable indexable insert	CN.. 1906..
Shim pins pack	259044 1
Lever	259015 1
Lever screw	259018 1
Shim punches pack	259047 1
Overall length L	250 mm
Head length L ₁	48 mm
Shank size	40 mm
ISO code toolholder	PCBNR/L 4040S19
Shim	259031 17
Functional width L ₄	35 mm
Insert size	19 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 1	259015 1
Lever Type 13	259015 13
Lever screw Type 1	259018 1
Lever screw Type 13	259018 13
Shim Type 16	259031 16
Shim Type 36	259031 36
Set of shim pins10 pieces Type 1	259044 1
Set of shim pins10 pieces Type 7	259044 7
Shim punches set10 pieces Type 1	259047 1