

**Mini burr Z7 – medium, diamond cut, Carbide, Type: AS0613****Order data**

Order number	546910 AS0613
GTIN	4045197724205
Item class	52D

Description**Version:**

HOLEX – burrs are manufactured from highest quality carbide with high wear-resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Carbide mini burr with shank Ø 3 mm.

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Head Ø	6.3 mm
Tooth type abbreviation	Z7
Toothing grit designation	medium
Type of cut	staggered teeth
Shape	AS0613
Shape description	Cylindrical with end cut
Overall length	45 mm
Shank Ø	3 mm
Head length	12.7 mm
Series	#Tooth configuration Z7

Tool material	Carbide
Type of product	Burr

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		