

Garant**Hard chromium coated high-performance file Cut 2, Type: 6****Order data**

Order number	519100 6
GTIN	4062406128623
Item class	51S

Description**Version:**

Hard chromium coated high-performance files of **HRC 67** cover a wide range of applications from soft materials such as **aluminium** through to very hard materials such as **high-alloy steels, stainless steels and ceramics**. Length without tang 100 mm.

Advantage:

- **High resistance to corrosion**
- **3-6 times longer working life than conventional files.**
- **Will not clog when filing very soft materials.**

Shape description: 3- square

Cross section: 9 mm

Technical description

Length without tang	100 mm
Cross section	9 mm
Shape description	3- square
Type of cut	Cut 2
Type of product	Multi-purpose file

User data

	Suitability	V_c	ISO code
Alu Mg	suitable		

Steel < 900 N/mm ²	suitable
Steel < 1400 N/mm ²	suitable
Steel < 55 HRC	suitable
Steel < 60 HRC	suitable
Steel < 67 HRC	suitable only under restricted conditions
INOX	suitable
Ti	suitable only under restricted conditions
GG(G)	suitable
CuZn	suitable
Plastic, GRP	suitable
Wood	suitable
Uni	suitable
dry	suitable