

Garant**Carbide-tipped hammer drill SDS-plus, Ø × Overall length: 5X110mm****Order data**

Order number	789040 5X110
GTIN	4062406135379
Item class	71C

Description**Version:**

Drill head with square cross-section. **4×90° geometry** with specially developed **equal height tips** and stable shoulders ensure precisely dimensioned holes for professional setting of anchors and secure plug attachment. 4-flute drilling heads for smooth drilling with low vibration and optimum guidance in the drilled hole. **Radially** shaped **reinforcement protection**: prevents jamming when hitting reinforcements and increases the working life. Sturdy **single-piece** carbide head with 4 cutters, inserted as a solid item in the core of the drill. Significantly reduced risk of breakage.

Advantage:

- **Short spiral starts ensure a smooth evacuation of the drill dust.**
- **Wear marks: for evaluation whether the tool is still suitable for drilling holes suitable for insertion of plugs.**
- **4×4 design permits a precise radial run-out and minimise wear and loss of frictional grip.**

Application:

For drilling concrete, natural stone, and masonry – with very high drilling comfort.

Technical description

Ø	5 mm
Overall length	110 mm
Working length	50 mm
Tool material	Carbide
Use with impact / without impact	Impact drilling
Shank	SDS Plus
Type of product	Masonry drill

