

**Garant****Carbide-tipped hammer drill SDS-plus, Ø × Overall length: 10X160mm****Order data**

|              |               |
|--------------|---------------|
| Order number | 789040 10X160 |
| GTIN         | 4062406135713 |
| Item class   | 71C           |

**Description****Version:**

Drill head with square cross-section. **4×90° geometry** with specially developed **equal height tips** and stable shoulders ensure precisely dimensioned holes for professional setting of anchors and secure plug attachment. 4-flute drilling heads for smooth drilling with low vibration and optimum guidance in the drilled hole. **Radially** shaped **reinforcement protection**: prevents jamming when hitting reinforcements and increases the working life. Sturdy **single-piece** carbide head with 4 cutters, inserted as a solid item in the core of the drill. Significantly reduced risk of breakage.

**Advantage:**

- **Short spiral starts ensure a smooth evacuation of the drill dust.**
- **Wear marks: for evaluation whether the tool is still suitable for drilling holes suitable for insertion of plugs.**
- **4×4 design permits a precise radial run-out and minimise wear and loss of frictional grip.**

**Application:**

For drilling concrete, natural stone, and masonry – with very high drilling comfort.

**Technical description**

|                                  |                 |
|----------------------------------|-----------------|
| Ø                                | 10 mm           |
| Working length                   | 100 mm          |
| Overall length                   | 160 mm          |
| Tool material                    | Carbide         |
| Use with impact / without impact | Impact drilling |
| Shank                            | SDS Plus        |
| Type of product                  | Masonry drill   |

