

**Garant****Soft-Pad pack, 20 pieces soft, 120×98×5 mm, Grit: 60****Order data**

Order number	557490 60
GTIN	4062406156008
Item class	51E

**Description****Version:**

**Soft pad** with foam structure for **pressure distribution**. Coated with aluminium oxide grit (A). Coated on 2 sides.

Reduced ingress of foreign material into the workpiece surface by a bonding structure free of solvents.

**Advantage:**

- **Resilient, no formation of kinks or folds.**
- **All sponges also suitable for wet grinding.**
- **Low tendency to clog, can be washed out.**

**Application:**

**Finish grinding of contours, edges, and at inaccessible places**, e.g. cleaning and preparation for painting. For wet and dry grinding.

Grinding medium code: A

Grit designation: medium

**Technical description**

Grit designation	medium
------------------	--------

Grit	60
Grinding media	Standard aluminium oxide (A)
Grinding medium code	A
Width	98 mm
Height	5 mm
Length	120 mm
Product name attribute	120×98×5 mm
Type of product	Abrasive sanding sponge

### User data

	Suitability	V <sub>c</sub>	ISO code
Alu Mg	suitable		
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable only under restricted conditions		
INOX	suitable		
Ti	suitable		
GG(G)	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
Wood	suitable		
Stone	suitable only under restricted conditions		
Paint	suitable		
Uni	suitable		
wet maximum	suitable		
dry	suitable		

