

**Garant****Soft-Pad pack, 20 pieces soft, 120×98×5 mm, Grit: 220****Order data**

|              |               |
|--------------|---------------|
| Order number | 557490 220    |
| GTIN         | 4062406156022 |
| Item class   | 51E           |

**Description****Version:**

**Soft pad** with foam structure for **pressure distribution**. Coated with aluminium oxide grit (A). Coated on 2 sides.

Reduced ingress of foreign material into the workpiece surface by a bonding structure free of solvents.

**Advantage:**

- **Resilient, no formation of kinks or folds.**
- **All sponges also suitable for wet grinding.**
- **Low tendency to clog, can be washed out.**

**Application:**

**Finish grinding of contours, edges, and at inaccessible places**, e.g. cleaning and preparation for painting. For wet and dry grinding.

Grinding medium code: A

Grit designation: super-fine

**Technical description**

|                  |            |
|------------------|------------|
| Grit designation | super-fine |
|------------------|------------|

|                        |                              |
|------------------------|------------------------------|
| Grit                   | 220                          |
| Grinding media         | Standard aluminium oxide (A) |
| Grinding medium code   | A                            |
| Width                  | 98 mm                        |
| Height                 | 5 mm                         |
| Length                 | 120 mm                       |
| Product name attribute | 120×98×5 mm                  |
| Type of product        | Abrasive sanding sponge      |

### User data

|                                | Suitability                               | V <sub>c</sub> | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg                         | suitable                                  |                |          |
| Steel < 900 N/mm <sup>2</sup>  | suitable                                  |                |          |
| Steel < 1400 N/mm <sup>2</sup> | suitable                                  |                |          |
| Steel < 55 HRC                 | suitable                                  |                |          |
| Steel < 60 HRC                 | suitable                                  |                |          |
| Steel < 67 HRC                 | suitable only under restricted conditions |                |          |
| INOX                           | suitable                                  |                |          |
| Ti                             | suitable                                  |                |          |
| GG(G)                          | suitable                                  |                |          |
| CuZn                           | suitable                                  |                |          |
| Plastic, GRP                   | suitable                                  |                |          |
| Wood                           | suitable                                  |                |          |
| Stone                          | suitable only under restricted conditions |                |          |
| Paint                          | suitable                                  |                |          |
| Uni                            | suitable                                  |                |          |
| wet maximum                    | suitable                                  |                |          |
| dry                            | suitable                                  |                |          |

