



Socket set 1/2 inch, Number of tools: 30



Order data

Order number	953751 30
GTIN	4062406157265
Item class	91A

Description

Version:

Popular tool sets in two-colour moulded PE rigid foam inlays. The closed-pore foam is oil-resistant and does not absorb liquids of any sort. Upper layer anthracite, under which the contrast colour of blue indicates if a tool is missing.

The rigid foam inlays fill 1/4 (10 G × 8 G or 250 × 200 mm) or 1/2 (20 G × 8 G or 500 × 200 mm) of the usable drawer area.

Suitable for:

New GARANT roller cabinets with full extension drawers and a new drawer module of **20 G × 16 G** or 500 × 400 mm (W × D).

Supplied with:

Rigid foam inlay, empty No. 952001 size 953751: 1 pc.

HOLEX bi-hexagon socket No. 642120 size 8; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 21; 22; 24; 27; 30; 32: 1 pc. each

HOLEX hexagon screwdriver bit No. 643220 size 4; 5; 6; 8; 10; 12; 14: 1 pc. each

HOLEX reversible ratchet, No. 640190 size 1/2: 1 pc.

HOLEX extension No. 641020 size 75; 125; 250: 1 pc. each

HOLEX T-handle No. 641320 size 295: 1 pc.

HOLEX universal joint No. 641620 size 1/2: 1 pc.

Smallest suitable drawer front height: 100 mm

Width: 200 mm

Depth: 500 mm

Width in G: 8

Depth in G: 20

Weight: 4.046 kg

Technical description

Depth in G	20
Weight	4.046 kg
Depth	500 mm
Number of tools	30
Width in G	8
Width	200 mm
Version	with socket
Rigid foam quality LD45, thickness	30 mm
Degree of fill of a drawer in units	8x20
Square drive	1/2 in
Smallest suitable drawer front height	100 mm
Type of product	Rigid foam inlay

Accessories

Screwdriver socket, inside hexagon, 1/2 inch Hexagon 6 mm	643220 6
Bi-hexagon socket, 1/2 inch Width across flats 14 mm	642120 14
Bi-hexagon socket, 1/2 inch Width across flats 27 mm	642120 27
Reversible ratchet, 1/2 inch with ejector Type 1/2	640190 1/2
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 8 mm	643220 8
Extension, 1/2 inch overall length 255 mm	641020 255
Extension, 1/2 inch overall length 130 mm	641020 130
Bi-hexagon socket, 1/2 inch Width across flats 8 mm	642120 8
Bi-hexagon socket, 1/2 inch Width across flats 18 mm	642120 18
Bi-hexagon socket, 1/2 inch Width across flats 24 mm	642120 24
Bi-hexagon socket, 1/2 inch Width across flats 10 mm	642120 10

Bi-hexagon socket, 1/2 inch Width across flats 15 mm	642120 15
Universal joint, 1/2 inch Type 1/2	641620 1/2
Bi-hexagon socket, 1/2 inch Width across flats 22 mm	642120 22
Bi-hexagon socket, 1/2 inch Width across flats 13 mm	642120 13
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 5 mm	643220 5
Rigid foam inlay for tool sets suitable for rigid foam set 953751	952001 953751
Extension, 1/2 inch overall length 75 mm	641020 75
Bi-hexagon socket, 1/2 inch Width across flats 19 mm	642120 19
Bi-hexagon socket, 1/2 inch Width across flats 11 mm	642120 11
Bi-hexagon socket, 1/2 inch Width across flats 12 mm	642120 12
Bi-hexagon socket, 1/2 inch Width across flats 30 mm	642120 30
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 4 mm	643220 4
Reversible ratchet, 1/2 inch with ejector	640220
Bi-hexagon socket, 1/2 inch Width across flats 17 mm	642120 17
T-handle, 1/2 inch overall length 295 mm	641320 295
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 12 mm	643220 12
Bi-hexagon socket, 1/2 inch Width across flats 21 mm	642120 21
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 14 mm	643220 14
Bi-hexagon socket, 1/2 inch Width across flats 16 mm	642120 16
Bi-hexagon socket, 1/2 inch Width across flats 32 mm	642120 32
Screwdriver socket, inside hexagon, 1/2 inch Hexagon 10 mm	643220 10