



Digital caliper ABS + accessories set, Measuring range: 150mm



Order data

Order number	412815 150
GTIN	4062406156497
Item class	42A

Description

Version:

Set consisting of a digital caliper and accessories set.

- **Digital caliper with absolute scale, no zeroing required. Large high-contrast digital display. The measuring faces are precision-lapped. With sturdy metal casing.**
- **Accessories set for digital caliper – permits measurement of recesses, slots and pitches between holes.**

Supplied with:

1× digital caliper No. 412821 size 150.

1 battery No. 081560 size CR2032.

1× accessory set No. 412747 size 3.5 **consisting of:**

2 pairs of contact point carriers short and long.

3 pairs of measuring tips with measuring discs \varnothing 6 mm, \varnothing 10 mm, \varnothing 12.5 mm.

2 pairs of measuring tips with anvil cones \varnothing 9 mm, 60° and \varnothing 12 mm, 60°.

1 pair of measuring tips with measuring cylinders \varnothing 1.5×9 mm.

1× spring system for constant gauging force.

1× hexagon key L-wrench.

1× depth extension base 75 mm.

Supplied in a sturdy plastic box.

Technical description

Number of batteries contained	1
Measured value saving	once-off setting of the zero position
Scale divisions	0.0005 in

Jaw length	40 mm
Calibration	A1
Standard	ISO 13385
Scale divisions	0.01 mm
Measuring range	0 - 150 mm
Article no of the battery / rechargeable battery fitted	081560 CR2032
Measurement face	precision lapped
Depth gauge available	yes
Reversible reading	mm / inch
Depth gauge	rectangular 3.7×1.3
Power supply	Battery-powered
Measurement deviation E MPE	±0.03 mm
Measurement technology	digital
Material	Stainless steel, INOX
all parts	hardened
Packaging	sturdy box
Type of product	Universal calipers

Services

CalibrationCalipers / depth gauges maximum measuring range 200 mm	021000 200
DAkkS calibrationCalipers / depth gauges maximum measuring range 200 mm	021010 200

Accessories

Depth base attachment	412710
Button cell / special battery Battery type CR2032	081560 CR2032
Accessories set for digital calipers maximum jaw thickness 3,5 mm	412747 3,5
Digital caliperABS Measuring range 150 mm	412821 150

Screw for depth gauge holder

412236