



## Manual vice for drilling machines, Jaw width A: 120mm



### Order data

Order number	365055 120
GTIN	4062406188641
Item class	32D

### Description

#### Version:

- Can be used horizontally, vertically or laterally.
- Sturdy and handy design.
- Jaws through hardened and ground.
- Uniform total length. (spindle retracts into handle!)
- Universal fastening capability due to long holes.
- Movable jaw with guides at the sides.
- Fixed jaw with three vertical prismatic and one horizontal prismatic section.
- With detachable crank.

#### Application:

For clamping components on drilling machines.

#### Material:

Cast iron body.

#### Accuracy:

Within 0.20 mm.

### Technical description

Jaw height C	39 mm
Clamping range b	128 mm
Weight	6.5 kg

Base body length a	225 mm
Overall height c	67 mm
Type of product	Drilling machine vice

---

## Accessories

Pair of spare jaws (2 pieces) for manual vice for drilling machines for type 120	365046 120
--	------------