

Garant**Short drill chuck Form F, HSK-F 63, Clamping range: 0,5-16mm****Order data**

Order number	307705 0,5-16
GTIN	4045197761156
Item class	33W

Description**Version:**

- For clockwise and anticlockwise rotation.
- With RFID/Balluffchip bore.

Concentricity $\leq 20 \mu\text{m}$.**Supplied with:****Clamping wrench** with T-handle.**Technical description**

Type	standard
Spare Torx® chuck key No. 625220	TX25
Overhang dimension A	102 mm
External Ø D	57 mm
Adapter	HSK-F 63
Arbor standard	DIN 69893-1
Arbor standard	DIN 69882-7
Arbor standard	ISO 12164-1
Shape	F
Balance quality G at rotational speed	G 2.5 at 25,000 rpm

Concentricity	≤ 20 µm
Type of product	Short drill chuck

Accessories

Screwdriver for Torx®, short, with T-handle Torx® profile TX25	625221 TX25
--	-------------