

Garant
**Clamping toolholder PCBNR 75°, for indexable inserts CN., right-hand,
Shank / insert size: 32/16mm**

Order data

Order number	250020 32/16
GTIN	4045197772114
Item class	21T

Technical description

ISO code toolholder	PCBNR/L 3232P16
suitable indexable insert	CN.. 1606..
Lever	259015 12
Shim pins pack	259044 6
Shim punches pack	259047 4
Functional width L ₄	27 mm
Shank size	32 mm
Insert size	16 mm
Overall length L	170 mm
Lever screw	259018 11
Head length L ₁	35 mm
Shim	259031 35
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 12	259015 12
Lever screw Type 11	259018 11
Shim Type 35	259031 35
Set of shim pins 10 pieces Type 6	259044 6
Shim punches set 10 pieces Type 4	259047 4