

**Garant**
**Clamping toolholder PCBNL 75°, for indexable inserts CN., left-hand, Shank / insert size: 25/16mm**

**Order data**

Order number	250021 25/16
GTIN	4045197772138
Item class	21T

**Technical description**

Shim	259031 35
Overall length L	150 mm
Lever	259015 12
Shim punches pack	259047 4
Functional width L <sub>4</sub>	22 mm
Lever screw	259018 11
Shim pins pack	259044 6
Insert size	16 mm
Head length L <sub>1</sub>	29 mm
Shank size	25 mm
suitable indexable insert	CN.. 1606..
ISO code toolholder	PCBNR/L 2525M16
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle $\kappa$	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Lever Type 12	259015 12
Lever screw Type 11	259018 11
Shim Type 35	259031 35
Set of shim pins 10 pieces Type 6	259044 6
Shim punches set 10 pieces Type 4	259047 4