

Garant
Clamping toolholder PCBNL 75°, for indexable inserts CN., left-hand, Shank / insert size: 32/16mm

Order data

Order number	250021 32/16
GTIN	4045197772145
Item class	21T

Technical description

suitable indexable insert	CN.. 1606..
Lever screw	259018 11
Insert size	16 mm
Shim	259031 35
Shim pins pack	259044 6
Head length L ₁	35 mm
Functional width L ₄	27 mm
ISO code toolholder	PCBNR/L 3232P16
Shim punches pack	259047 4
Lever	259015 12
Overall length L	170 mm
Shank size	32 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 12	259015 12
Lever screw Type 11	259018 11
Shim Type 35	259031 35
Set of shim pins 10 pieces Type 6	259044 6
Shim punches set 10 pieces Type 4	259047 4