

Garant
**Clamping toolholder PCSNR 45°, for indexable inserts CN., right-hand,
Shank / insert size: 32/19mm**

Order data

Order number	250024 32/19
GTIN	4045197772183
Item class	21T

Technical description

Insert size	19 mm
Head length L ₁	40 mm
Shank size	32 mm
Overall length L	170 mm
Shim punches pack	259047 5
Lever	259015 13
Lever screw	259018 13
Shim	259031 36
Shim pins pack	259044 7
suitable indexable insert	CN.. 1906..
Functional width L ₄	40 mm
ISO code toolholder	PCSNR/L 3232P19
Standard	Works standard
Application type	right-hand
Through-coolant	no

Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 13	259015 13
Lever screw Type 13	259018 13
Shim Type 36	259031 36
Set of shim pins 10 pieces Type 7	259044 7