

Garant
Clamping toolholder PCSNL 45°, for indexable inserts CN., left-hand, Shank / insert size: 25/16mm

Order data

Order number	250025 25/16
GTIN	4045197772190
Item class	21T

Technical description

Overall length L	150 mm
Head length L ₁	33 mm
Shim	259031 35
Functional width L ₄	32 mm
Lever screw	259018 11
Shim pins pack	259044 6
Lever	259015 12
Shank size	25 mm
ISO code toolholder	PCSNR/L 2525M16
Shim punches pack	259047 4
Insert size	16 mm
suitable indexable insert	CN.. 1606..
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 12	259015 12
Lever screw Type 11	259018 11
Shim Type 35	259031 35
Set of shim pins 10 pieces Type 6	259044 6
Shim punches set 10 pieces Type 4	259047 4