

Garant
Clamping toolholder PCSNL 45°, for indexable inserts CN., left-hand, Shank / insert size: 32/16mm

Order data

Order number	250025 32/16
GTIN	4045197772305
Item class	21T

Technical description

Shank size	32 mm
Lever	259015 12
Head length L ₁	34 mm
Shim pins pack	259044 6
Insert size	16 mm
ISO code toolholder	PCSNR/L 3232P16
Lever screw	259018 11
Overall length L	170 mm
Shim punches pack	259047 4
Shim	259031 35
suitable indexable insert	CN.. 1606..
Functional width L ₄	40 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle κ	45 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 12	259015 12
Lever screw Type 11	259018 11
Shim Type 35	259031 35
Set of shim pins 10 pieces Type 6	259044 6
Shim punches set 10 pieces Type 4	259047 4