

Garant

**Clamping toolholder SCRCR 75°, for indexable inserts CC., right-hand,
Shank / insert size: 10/06mm**



Order data

Order number	260004 10/06
GTIN	4045197772480
Item class	21T

Technical description

Shank size	10 mm
suitable indexable insert	CC.. 0602..
Pack of insert screws	269028 22
Functional width L ₄	11 mm
Head length L ₁	10 mm
Overall length L	70 mm
ISO code toolholder	SCRCR/L 1010E06
Insert size	6 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning

Type of product	Boring bar
-----------------	------------

Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8