

Garant

**Clamping toolholder SCRCR 75°, for indexable inserts CC., right-hand,
Shank / insert size: 16/12mm**



Order data

Order number	260004 16/12
GTIN	4045197772527
Item class	21T

Technical description

Insert size	12 mm
Shank size	16 mm
ISO code toolholder	SCRCR/L 1616H12
Shim screw	269013 5
Pack of insert screws	269028 16
Head length L ₁	20 mm
suitable indexable insert	CC.. 1204..
Overall length L	100 mm
Shim	269005 6
Functional width L ₄	17 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	75 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 6	269005 6
Shim screw Type 5	269013 5
Set of insert screws Type 16	269028 16
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 20IP	674252 20IP