

Garant
**Clamping toolholder SCRCR 75°, for indexable inserts CC., right-hand,
Shank / insert size: 20/12mm**

Order data

Order number	260004 20/12
GTIN	4045197772534
Item class	21T

Technical description

Shim screw	269013 5
Functional width L ₄	22 mm
Insert size	12 mm
suitable indexable insert	CC.. 1204..
ISO code toolholder	SCRCR/L 2020K12
Shim	269005 6
Shank size	20 mm
Overall length L	125 mm
Pack of insert screws	269028 16
Head length L ₁	20 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	75 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 6	269005 6
Shim screw Type 5	269013 5
Set of insert screws Type 16	269028 16
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 20IP	674252 20IP