

**Garant**

**Clamping toolholder SCRCL 75°, for indexable inserts CC., left-hand, Shank / insert size: 10/06mm**



## Order data

Order number	260005 10/06
GTIN	4045197772565
Item class	21T

## Technical description

Pack of insert screws	269028 22
ISO code toolholder	SCRCR/L 1010E06
Insert size	6 mm
suitable indexable insert	CC.. 0602..
Functional width L <sub>4</sub>	11 mm
Overall length L	70 mm
Shank size	10 mm
Head length L <sub>1</sub>	10 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning

Type of product	Boring bar
-----------------	------------

---

## Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8