

Garant

Clamping toolholder SCRCL 75°, for indexable inserts CC., left-hand, Shank / insert size: 16/09mm



Order data

Order number	260005 16/09
GTIN	4045197772589
Item class	21T

Technical description

Shim screw	269013 2
ISO code toolholder	SCRCR/L 1616H09
Pack of insert screws	269028 2
Functional width L ₄	17 mm
suitable indexable insert	CC.. 09T3..
Shim	269005 1
Overall length L	100 mm
Insert size	9 mm
Shank size	16 mm
Head length L ₁	15 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	75 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim Type 1	269005 1
Shim screw Type 2	269013 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15