

Garant

Clamping toolholder SCRCL 75°, for indexable inserts CC., left-hand, Shank / insert size: 25/12mm



Order data

| | |
|--------------|---------------|
| Order number | 260005 25/12 |
| GTIN | 4045197772626 |
| Item class | 21T |

Technical description

| | |
|---------------------------------|-------------------------------|
| Insert size | 12 mm |
| Shank size | 25 mm |
| ISO code toolholder | SCRCR/L 2525M12 |
| Shim | 269005 6 |
| Head length L ₁ | 20 mm |
| Functional width L ₄ | 27 mm |
| Overall length L | 150 mm |
| Shim screw | 269013 5 |
| Pack of insert screws | 269028 16 |
| suitable indexable insert | CC.. 1204.. |
| Standard | Works standard |
| Application type | left-hand |
| Through-coolant | no |
| Setting angle κ | 75 degrees |
| Application | External longitudinal turning |

| | |
|-----------------|-------------------------------|
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|--|-------------|
| Shim Type 6 | 269005 6 |
| Shim screw Type 5 | 269013 5 |
| Set of insert screws Type 16 | 269028 16 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |
| PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 20IP | 674252 20IP |