

Garant

Steel boring bar A.. SVJBR 142°, for indexable inserts VB.., right-hand, Shank Ø / insert size: 20/11mm


Order data

Order number	261124 20/11
GTIN	4045197778376
Item class	21T

Technical description

Overall length L	180 mm
Pack of insert screws	269028 7
Neck width L ₄	11 mm
Head length L ₁	38 mm
ISO code toolholder	A20Q SVJBR/L11
Centre offset L ₃	2 mm
Minimum pre-drill Ø D _{min}	25 mm
Setting angle κ	142 degrees
Clamping height L ₂	19 mm
suitable indexable insert	VB.. 1103..
Insert size	11 mm
Shank Ø D _s	20 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8