

**Garant**

**Steel boring bar A.. SVJBL 142°, for indexable inserts VB.., left-hand, Shank Ø / insert size: 16/11mm**


**Order data**

Order number	261125 16/11
GTIN	4045197778390
Item class	21T

**Technical description**

Clamping height $L_2$	15 mm
suitable indexable insert	VB.. 1103..
Overall length L	150 mm
Neck width $L_4$	9.5 mm
Setting angle $\kappa$	142 degrees
ISO code toolholder	A16M SVJBR/L11
Pack of insert screws	269028 7
Head length $L_1$	31.4 mm
Centre offset $L_3$	2 mm
Insert size	11 mm
Minimum pre-drill $\varnothing D_{\min}$	22 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3xD
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8