

Garant

Steel boring bar A.. SVJBL 142°, for indexable inserts VB.., left-hand, Shank Ø / insert size: 20/11mm


Order data

Order number	261125 20/11
GTIN	4045197778406
Item class	21T

Technical description

Neck width L_4	11 mm
Clamping height L_2	19 mm
Pack of insert screws	269028 7
Head length L_1	38 mm
Setting angle κ	142 degrees
suitable indexable insert	VB.. 1103..
Centre offset L_3	2 mm
ISO code toolholder	A20Q SVJBR/L11
Overall length L	180 mm
Minimum pre-drill $\varnothing D_{\min}$	25 mm
Insert size	11 mm
Shank $\varnothing D_s$	20 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes

Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 7	269028 7
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8