



Face mill arbor extension short, Spigot \varnothing d1: 16mm



Order data

Order number	301105 16
GTIN	4045197778420
Item class	32B

Description

Version:

Mounting spigot, bore and all contact surfaces are ground at the collar.

Application:

For flexible extensions of face mill arbors. Economy alternative to expensive custom-made arbors. 3 options for use: short (45 mm) or long (70 mm) extension or maximum extension by combining two short extensions (2×45 mm).

Supplied with:

Suitable lock screw.

Optional extras:

Special toggle spanner No. 309840.

Replacement screw No. 301107.

Technical description

Overall length L	45 mm
Spigot \varnothing d ₁	16 mm
External \varnothing D	38 mm
A	17 mm
Standard	DIN 6357

Concentricity	≤ 3 µm
Type of product	Extension

Accessories

Toggle spanner for mandrel Ø 40 mm	309840 40
Clamping screw for extension 2 × 45 mm for spigot Ø D1 32 mm	301109 32
Toggle spanner for mandrel Ø 16 mm	309840 16
Toggle spanner for mandrel Ø 60 mm	309840 60
Clamping screw for extension 2 × 45 mm for spigot Ø D1 27 mm	301109 27
Clamping screw for extension 45 mm for spigot Ø D1 16 mm	301107 16
Toggle spanner for mandrel Ø 22 mm	309840 22
Clamping screw for extension 45 mm for spigot Ø D1 40 mm	301107 40
Clamping screw for extension 45 mm for spigot Ø D1 22 mm	301107 22
Toggle spanner for mandrel Ø 50 mm	309840 50
Clamping screw for extension 2 × 45 mm for spigot Ø D1 16 mm	301109 16
Clamping screw for extension 45 mm for spigot Ø D1 27 mm	301107 27
Clamping screw for extension 45 mm for spigot Ø D1 32 mm	301107 32
Toggle spanner for mandrel Ø 13 mm	309840 13
Toggle spanner for mandrel Ø 27 mm	309840 27
Clamping screw for extension 2 × 45 mm for spigot Ø D1 22 mm	301109 22
Clamping screw for extension 2 × 45 mm for spigot Ø D1 40 mm	301109 40

Locking screw for extension for mandrel length L 45 mm	301111 45
Toggle spanner for mandrel Ø 32 mm	309840 32