

Garant**Eccentric clamp, Thread M: M10****Order data**

Order number	370001 M10
GTIN	4045197782373
Item class	310

Description**Version:**

- Hexagon steel washer with eccentric steel screw.
- Clamping of workpieces of any shape.
- 6 different geometries at the clamping faces: 1. Vee with 150° opening angle 2. Longitudinally grooved 3. Smooth step 4. Serrated 5. Smooth 6. Smooth coated.
- Requires less space, so few interference contours.

Version of the advertising text:

- For clamping workpieces of any shape.
- 6 different geometries on the drive flats.

Application:

Suitable for clamping blanks and finished parts

Note:

A hexagon L-wrench size 7 is required!

Technical description

Thread M	M10
Internal hexagon AF ₁	7 mm

Washer height H	10 mm
Thread length L	9 mm
Eccentric travel S_1	1.6 mm
Dimension A	12.7 mm
Hexagon washer AF	25 mm
Clamping force	9 kN
maximum tightening torque	28 Nm
Type of product	Eccentric clamp