

Garant
Clamping toolholder PCBNL 75°, for indexable inserts CN., left-hand, Shank / insert size: 16/09mm

Order data

Order number	250021 16/09
GTIN	4045197781840
Item class	21T

Technical description

suitable indexable insert	CN.. 09T3..
Lever screw	259018 6
Shank size	16 mm
Lever	259015 9
Functional width L ₄	16 mm
Shim punches pack	259047 3
Insert size	9 mm
ISO code toolholder	PCBNR/L 1616H09
Head length L ₁	20 mm
Shim	259031 27
Overall length L	100 mm
Shim pins pack	259044 5
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 9	259015 9
Lever screw Type 6	259018 6
Shim Type 27	259031 27
Set of shim pins 10 pieces Type 5	259044 5
Shim punches set 10 pieces Type 3	259047 3