

Garant
Clamping toolholder PCBNL 75°, for indexable inserts CN., left-hand, Shank / insert size: 20/09mm

Order data

Order number	250021 20/09
GTIN	4045197781857
Item class	21T

Technical description

Shim pins pack	259044 5
Functional width L ₄	20 mm
Lever	259015 9
suitable indexable insert	CN.. 09T3..
ISO code toolholder	PCBNR/L 2020K09
Shim punches pack	259047 3
Shim	259031 27
Lever screw	259018 6
Insert size	9 mm
Shank size	20 mm
Overall length L	125 mm
Head length L ₁	21 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 9	259015 9
Lever screw Type 6	259018 6
Shim Type 27	259031 27
Set of shim pins 10 pieces Type 5	259044 5
Shim punches set 10 pieces Type 3	259047 3