

Garant**Clamping toolholder PCBNL 75°, for indexable inserts CN., left-hand, Shank / insert size: 25/09mm****Order data**

Order number	250021 25/09
GTIN	4045197781864
Item class	21T

Technical description

Functional width L ₄	25 mm
Insert size	9 mm
Lever screw	259018 6
Head length L ₁	21 mm
Shim	259031 27
Overall length L	150 mm
ISO code toolholder	PCBNR/L 2525M09
suitable indexable insert	CN.. 09T3..
Shim punches pack	259047 3
Shim pins pack	259044 5
Shank size	25 mm
Lever	259015 9
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 9	259015 9
Lever screw Type 6	259018 6
Shim Type 27	259031 27
Set of shim pins 10 pieces Type 5	259044 5
Shim punches set 10 pieces Type 3	259047 3