

**Garant**
**Clamping toolholder PCKNL 75°, for indexable inserts CN., left-hand, Shank / insert size: 20/09mm**

**Order data**

Order number	250023 20/09
GTIN	4045197782618
Item class	21T

**Technical description**

Overall length L	125 mm
ISO code toolholder	PCKNR/L 2020K09
Insert size	9 mm
Functional width L <sub>4</sub>	25 mm
Lever screw	259018 6
Lever	259015 9
Shim	259031 27
suitable indexable insert	CN.. 09T3..
Head length L <sub>1</sub>	20 mm
Shank size	20 mm
Shim punches pack	259047 3
Shim pins pack	259044 5
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle $\kappa$	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Lever Type 9	259015 9
Lever screw Type 6	259018 6
Shim Type 27	259031 27
Set of shim pins 10 pieces Type 5	259044 5
Shim punches set 10 pieces Type 3	259047 3