

**Garant**
**Clamping toolholder PCKNL 75°, for indexable inserts CN., left-hand, Shank / insert size: 25/16mm**

**Order data**

Order number	250023 25/16
GTIN	4045197782632
Item class	21T

**Technical description**

Insert size	16 mm
Shim punches pack	259047 4
Shim pins pack	259044 6
suitable indexable insert	CN.. 1606..
Shank size	25 mm
Lever screw	259018 11
Functional width L <sub>4</sub>	32 mm
ISO code toolholder	PCKNR/L 2525M16
Shim	259031 35
Head length L <sub>1</sub>	30 mm
Overall length L	150 mm
Lever	259015 12
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle $\kappa$	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Lever Type 12	259015 12
Lever screw Type 11	259018 11
Shim Type 35	259031 35
Set of shim pins 10 pieces Type 6	259044 6
Shim punches set 10 pieces Type 4	259047 4