

Garant
Clamping toolholder PCKNL 75°, for indexable inserts CN., left-hand, Shank / insert size: 32/16mm

Order data

Order number	250023 32/16
GTIN	4045197782649
Item class	21T

Technical description

Lever	259015 12
Shim punches pack	259047 4
Head length L ₁	34 mm
Shank size	32 mm
Overall length L	170 mm
Shim pins pack	259044 6
Lever screw	259018 11
Insert size	16 mm
Functional width L ₄	40 mm
Shim	259031 35
ISO code toolholder	PCKNR/L 3232P16
suitable indexable insert	CN.. 1606..
Standard	Works standard
Application type	left-hand
Through-coolant	no

Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Lever Type 12	259015 12
Lever screw Type 11	259018 11
Shim Type 35	259031 35
Set of shim pins 10 pieces Type 6	259044 6
Shim punches set 10 pieces Type 4	259047 4